

Garant**DNMG 150608, Grade: HB725-1**

Order data

Order number	250762 HB725-1
GTIN	4062406750602
Item class	21G

Description

DNMG 150608 HB725-1 Grade: HB725-1
Chip breaker: UM1
Tolerance: M
Cutting depth a_p : 0.2 - 6 mm
Feed f : 0.05 - 0.6 mm/rev.
Cutting speed v_c main application: 50 - 250 m/min

Technical description

Cutting depth a_p	0.2 - 6 mm
Tolerance	M
Number of changes/inserts	4
Chip breaker	UM1
Corner radius	0.8 mm
Grade	HB725-1

Cutting conditions	slightly interrupted
Cutting speed v_c main application	50 - 250 m/min
Feed f	0.05 - 0.6 mm/rev.
Tool material	Carbide
ISO code indexable insert	DNMG 150608
Finishing/roughing assignment	Finishing
Main application	UNI
Type of product	Indexable insert for turning