



Laser distance meter, Type: GLM150-27C



Order data

Order number	465560 GLM150-27C
GTIN	4059952614304
Item class	46T

Description

Version:

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof. Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Precision over long distances. Measurements transmitted via Bluetooth to the new MeasureOnApp. Save images in the internal memory and transfer images to the PC via USB. Integrated Li-ion battery makes for very flexible working and improves sustainability.

Version of the advertising text:

Laser distance measurement device with robust, shock-resistant casing, splash-proof and dust-proof. Illuminated three-row display for optimum legibility. Laser class 2 to IEC 825-1. Stand socket thread 1/4 inch. The integral 360° inclination sensor shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement. Create a digital floor plan, import existing floor plans, edit them and export the result together with simple building site dimensioning. Data transfer via Bluetooth®.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes protective case. Incl. Li-ion battery + micro-USB cable.

Optional extras:

Measuring stand No. 468558.

Technical description

Number of rechargeable batteries contained	1
Surface and volume calculations	yes
Weight	210 g
Length	142 mm
Threaded socket for stand	1/4 in
Battery capacity	3.12 Ah
Clinometer	360 degrees
indirect measurements (Pythagoras)	yes
Width	64 mm
Recall last measurements	yes
Nominal voltage	3.6 V
Measuring accuracy	±1.5 mm
Minimum / maximum measurements	yes
Height	28 mm
Type of rechargeable battery	Lithium-ion
Addition/subtraction	yes
Power supply	Li-ion battery
Range	150 m
Manufacturer's designation	GLM150-27C
Interface	Bluetooth interface
Interface	USB interface
Power supply	Rechargeable battery-powered
IP Index of Protection	IP 54
Series	GLM150-27C
Digital target search	yes
Laser class to IEC 825–1	2
Type of product	Distance meter

