

Garant
WNMG 080412, Grade: HB725-1


Order data

Order number	252072 HB725-1
GTIN	4062406765729
Item class	21G

Description

WNMG 080412 HB725-1 Grade: HB725-1

Chip breaker: UM1

Tolerance: M

Cutting depth a_p : 0.2 - 6 mm

Feed f : 0.05 - 0.6 mm/rev.

Cutting speed v_c main application: 50 - 250 m/min

Technical description

Main application	UNI
ISO code indexable insert	WNMG 080412
Feed f	0.05 - 0.6 mm/rev.
Corner radius	1.2 mm
Cutting speed v_c main application	50 - 250 m/min
Grade	HB725-1
Finishing/roughing assignment	Finishing

Chip breaker	UM1
Number of changes/inserts	6
Cutting depth a_p	0.2 - 6 mm
Tool material	Carbide
Cutting conditions	slightly interrupted
Tolerance	M
Type of product	Indexable insert for turning