

**Self-levelling cross-hair laser GLL, Type: 2-15G****Order data**

Order number	468490 2-15G
GTIN	4059952511054
Item class	46T

**Description****Version:**

Compact cross-hair laser with self-levelling laser lines. Quick horizontal and vertical alignment of lines. Robust design soft-grip coating protects against impact loads. Dust-proof and splash-proof. In addition, two vertical plumb-line points.

One horizontal and 2 vertical 360° lines permit a wide range of new applications for simultaneous marking, alignment and levelling indoors. Large working range up to 120 m using the LR 7 Professional receiver (accessories). **IP64 protection.** Sturdy construction with recessed glass and rubberised casing for use under demanding working conditions. Convenient, quick and secure attachment thanks to the LB 10 Professional universal holder with very strong magnets.

**Green laser lines** for optimum visibility even under poor lighting conditions.

**Function:**

IP64: Protected against splashed water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

4× battery No. 081561 LR6, LB 10 universal holder, laser target plate, protective bag.

**Technical description**

Height	115 mm
Range	15 m
Threaded socket for stand	1/4 in
Power supply	Battery-powered
Manufacturer's designation	GLL 2-15 G
Number of batteries contained	4
Error limit	±0.3 mm/m
Levelling range	±4 degrees
Laser class	2
Weight	570 g
Length	126 mm
Article no of the battery / rechargeable battery fitted	081561 LR6
Width	63 mm
Colour of the laser	green
IP Index of Protection	IP 64
Type of product	Cross laser

---

## Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------