

Garant
WNMG 080408, Grade: HB725-1


Order data

Order number	252070 HB725-1
GTIN	4062406765712
Item class	21G

Description

WN.G 080408 HB725-1 Grade: HB725-1

Chip breaker: UN1

Tolerance: M

Cutting depth a_p : 0.2 - 6 mm

Feed f : 0.05 - 0.6 mm/rev.

Cutting speed v_c main application: 50 - 250 m/min

Technical description

Feed f	0.05 - 0.6 mm/rev.
ISO code indexable insert	WNMG 080408
Cutting speed v_c main application	50 - 250 m/min
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting conditions	slightly interrupted
Cutting depth a_p	0.2 - 6 mm

Number of changes/inserts	6
Chip breaker	UN1
Grade	HB725-1
Corner radius	0.8 mm
Main application	UNI
Tool material	Carbide
Type of product	Indexable insert for turning