

Garant**RC.T 0602, Grade: HB725-1**

Order data

Order number	260620 HB725-1
GTIN	4062406765996
Item class	21G

Description

RC.T 0602 HB725-1 Chip breaker: UM1
Tolerance: M
Cutting depth a_p : 0.5 - 2 mm
Feed f : 0.1 - 0.3 mm/rev.
Cutting speed v_c main application: 60 - 230 m/min

Technical description

Tolerance	M
Grade	HB725-1
ISO code indexable insert	RCMT 0602
Number of changes/inserts	4
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	60 - 230 m/min
Tool material	Carbide

Main application	UNI
Cutting conditions	slightly interrupted
Chip breaker	UM1
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.5 - 2 mm
Type of product	Indexable insert for turning