

**Garant**
**DC.T 11T308, Grade: HB725-1**


### Order data

Order number	260464 HB725-1
GTIN	4062406765989
Item class	21G

### Description

DC.T 11T308 HB725-1 Grade: HB725-1  
 Chip breaker: UM1  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.2 - 4 mm  
 Feed  $f$ : 0.05 - 0.5 mm/rev.  
 Cutting speed  $v_c$  main application: 50 - 250 m/min

### Technical description

Tool material	Carbide
Grade	HB725-1
Cutting depth $a_p$	0.2 - 4 mm
Number of changes/inserts	2
Cutting speed $v_c$ main application	50 - 250 m/min
Main application	UNI
ISO code indexable insert	DCMT 11T308

Tolerance	M
Chip breaker	UM1
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.8 mm
Type of product	Indexable insert for turning