



Self-levelling cross-hair laser LINO, Type: L6GS



Order data

Order number	468486 L6GS
GTIN	7640180530657
Item class	47C

Description

Version:

Robust, ergonomic plastic casing; proof against dust and splashed water. **With green laser lines for optimum visibility. Up to 400% better visibility than red laser lines.**

Self-levelling multi-mains laser with 3× 360° laser lines. One horizontal and two vertical 360° laser lines. Laser lines thin, sharp and clearly visible. Laser power can be set in 3 stages for better visibility or longer operating time. Self-levelling over long distances in the event of inclined positions. Time saving by easy setting up of the zero point. Fixed zero point thanks to integral base. Simple and precise alignment of the laser lines by $\pm 10^\circ$. Memory function of personal settings. Dust-proof and splash-proof. The triple power-supply concept permits uninterrupted work. Can optionally be operated with Li-ion battery, AA batteries or power supply unit.

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Li-ion battery, charger with mains adaptor, laser target plate, bag.

Technical description

Width	60 mm
Battery capacity	5.2 Ah
Levelling range	±4 degrees
Threaded socket for stand	1/4 UNC in
Type of rechargeable battery	Lithium-ion
Colour of the laser	green
Depth	100 mm
Power supply	Battery-powered
Power supply	Rechargeable battery-powered
Power supply	Mains-powered
IP Index of Protection	IP 54
Series	LINO
Weight	530 g
Number of rechargeable batteries contained	1
Range	35 m
Error limit	±0.2 mm/m
Range with receiver	70 m
Height	110 mm
Diameter with receiver	140 mm
Working time	11 h
Type of product	Cross laser