



Shrink-fit chuck Power Shrink Chuck with Safe-Lock, SK 50 short, Clamping range \varnothing D1: 16mm



Order data

Order number	302307 16
GTIN	4034221062765
Item class	34I

Description

Version:

Shrink-fit chuck for very high metal removal rates during high-performance cutting (HPC). The optimised design combines excellent stiffness with vibration damping. This protects the machine, spindle and tool.

- **Safe-Lock tool pull-out protection prevents the tool being pulled out accidentally.**
- **Higher metal removal rate due to higher speeds, higher feed rates and greater cutting depth.**
- **Shorter machining times.**
- **Runs more smoothly, which improves the surface quality and protects the tool, spindle and machine.**
- **With tapped holes for balancing with screws.**
- **With pluggable Cool Jet holes.**
- **With length adjustment screw (adjustment path 10 mm).**

Application:

For clamping tools with parallel shank to h6 tolerance **with Safe-Lock ground surface**. Suitable for all types of shrink-fit unit such as inductive, contact and hot air shrink-fit units.

Optional extras:

For milling cutters with Safe-Lock clamping flat, see solid carbide milling cutters. Pull studs (PS) No. 308600 – 308800, PS wrenches No. 308820 – 308835. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Note:

Other shrink-fit chucks with **Safe-Lock** available on request.

Technical description

Overhang dimension A	80 mm
Cooling channel bore	lockable
Clamping $\varnothing D_1$	16 mm
External $\varnothing D$	43 mm
$\varnothing D_2$	33.3 mm
maximum clamping depth L_E	50 mm
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	3 μm
Machining strategy	HPC
Machining strategy	HSC
Tool pull-out protection	Safe-Lock h6
Type of product	Shrink-fit chuck