


Garant
CC.T 09T304, Grade: HB7315-1


Order data

Order number	260058 HB7315-1
GTIN	4062406769925
Item class	21G

Description

CC.T 09T304 HB7315-1 Grade: HB7315-1
 Chip breaker: AF
 Tolerance: G
 Cutting depth a_p : 0.05 - 0.5 mm
 Feed f : 0.03 - 0.1 mm/rev.
 Cutting speed v_c main application: 120 - 600 m/min

Technical description

Cutting depth a_p	0.05 - 0.5 mm
Cutting conditions	continuous
Chip breaker	AF
Main application	N
Feed f	0.03 - 0.1 mm/rev.
Finishing/roughing assignment	Finishing
Number of changes/inserts	2

Cutting speed v_c main application	120 - 600 m/min
Grade	HB7315-1
ISO code indexable insert	CCGT 09T304
Tolerance	G
Corner radius	0.4 mm
Tool material	Carbide
Type of product	Indexable insert for turning