

JEPSON POWER**Cordless metal cutting hand-held circular saw, Type: 8203E****Order data**

Order number	078235 8203E
GTIN	4260052468050
Item class	07E

Description**Version:**

Powerful metal-cutting circular saws for for low-burr and safe sawing of profiles and pipes made from steel, non-ferrous metals, sheet metal, metal plates and sandwich panels **without generating sparks.**

- **No need to use cooling lubricants.**
- **No reworking necessary.**
- **Cuts in seconds.**

Hand DRY Cutter 8203E cordless metal cutting hand-held circular saw.

- **Ideal for sawing steel, sheet steel, sandwich panels, metal plates, pipes and profiles made from steel, non-ferrous metals, composite materials, up to a thickness of 6 mm.**
- **Chip catcher for clean working.**
- **Equipped with a dia. 203/48Z carbide-tipped saw blade "LBS shock-resistant" for maximum tool life and quality.**

Supplied with:

Includes 2 high-performance 18 V LiHD 5.5 A batteries, saw blade, charger and case.

Note:

Compatible with the Cordless Alliance System (CAS), a cross-manufacturer battery pack system of leading power tool brands. Suitable saw blades can be found under No. 078243.

Technical description

maximum cutting depth 90°	67 mm
maximum speed	3500 min ⁻¹
Saw blade Ø	203 mm
maximum cutting depth 45°	42 mm
Power supply	Rechargeable battery-powered
Manufacturer's designation	8203E
Number of rechargeable batteries contained	2
Type of rechargeable battery	Lithium-ion
Weight without battery	5.4 kg
Battery capacity	5.5 Ah
Battery voltage	18 V
Type of product	Saw