

Garant
GARANT Master Mute boring bar shank vibration damping, 15×D, System / shank Ø: GL/16

Order data

Order number	264874 GL/16
GTIN	4062406770198
Item class	29E

Description
Version:

Shank carbide reinforced.

Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + \text{ cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: GL

Overall length L: 268 mm

non-clamping range S: 102 mm

recommended clamping length: 64 mm

Assembly bolt set: 269026 1

Technical description

Assembly bolt set	269026 1
recommended clamping length	64 mm
System	GL
non-clamping range S	102 mm
Overall length L	268 mm
Series	Master Mute

Boring depth up to	15xD
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks