

Garant**Burr, coated GARANT Master Steel – coarse, Carbide AlCrN, Type: D1210****Order data**

Order number	547400 D1210
GTIN	4062406774110
Item class	51D

Description**Version:**

The innovative tooth geometry permits very high metal removal rates combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

The newly developed innovative tooth geometry permits high metal removal rates combined with extremely smooth running and very good guidance. The optimum chip formation (no pointed chips) achieves high surface quality in roughing and finishing applications.

With high-performance coating for longer tool life, less heat input, better chip evacuation.

- **High material removal rate.**
- **Smooth running.**
- **High-performance coating for low thermal stress, longer tool life, and improved chip evacuation.**
- **State-of-the-art substrate optimised for steel materials.**
- **Maximum tool life.**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Application:

Optimised for **use on steel and steel castings**.

Suitable for use with power tools and industrial robots on all steel materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Note:

Materials with poor heat conductivity; reduce speed to avoid overheating of the burr and smearing.

Technical description

Tooth type abbreviation	Z steel
Head Ø	12 mm
Head length	10 mm
Overall length	51 mm
Shape	D1210
Shank Ø	6 mm
Toothing grit designation	coarse
Shape description	ball
Series	GARANT Master Steel
Tool material	Carbide AlCrN
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		