

**Garant**
**HCT digital depth gauge IP67 with Bluetooth, Measuring range: 300mm**

**Order data**

Order number	418685 300
GTIN	4062406773984
Item class	41A

**Description**
**Version:**

**Very large high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 20 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface**. The measuring faces are precision-lapped. Measuring beam has a slender hardened measuring pin at the front,  $\varnothing$  1.5 mm, 5 mm long. With preset (dimension selection in advance).

IP67 HCT digital depth gauge with Bluetooth 5.0. **Very large high-contrast LCD display with 11.5 mm character height.** Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point. 2-component body with **non-slip Haptoprene surface**. The measuring faces are precision-lapped. Measuring beam has a slender hardened measuring pin at the front,  $\varnothing$  1.5 mm, 5 mm long. With preset (dimension selection in advance).

Version **with Bluetooth**. Compatible with the optional HCT (Hoffmann Group Connected Tools) mobile app. Available free of charge for Android and iOS. Can also be used via a Human Interface Device (HID).

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size CR2032.

**Optional extras:**

Extension base 320 mm long No. 418689, measuring tip for caliper jaws No. 418630

## Technical description

IP Index of Protection	IP 67
Calibration	A1
Interface	Bluetooth interface
Reversible reading	0.01 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Series	HCT
Wireless application	HID (Human Interface Device)
Wireless application	HCT Mobile App
Wireless application	HCT Windows app
Power supply	Battery-powered
Bridge length	100 mm
Reversible reading	0.0005 in
Cross-section measuring beam	16×3.5 mm
Battery type	Button cell
Number of batteries contained	1
Measurement deviation E MPE	±0.03 mm
Standard	ISO 13385
Reversible reading	mm / inch
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Depth gauge

## Services

Calibration Vernier hook depth gauge maximum measuring range 300 mm	021220 300
	021230 300

DAkKS calibration Vernier hook depth gauge maximum  
measuring range 300 mm

### Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Cover for digital calipers Type B	412237 B
Screw for depth gauge holder	412236