



Three-jaw lathe chuck steel short taper mount, DIN 702-3, Outer Ø A / taper: 200/5mm



Order data

Order number	310705 200/5
GTIN	4019208025575
Item class	36S

Description

Version:

- **Manual chucks with gear scroll, centrally clamping.**
- **Weight-reduced body of steel.**
- **Gear scroll drop-forged, balanced, and hardened.**
- **Flanks of scroll and of jaw serrations are ground.**
- **High concentricity.**

Application:

The chuck is always fitted to the spindle nose directly without an intermediate flange.

For spindle noses DIN 55027 **with studs and collar nuts.**

Standard:

DIN 702-3.

Supplied with:

1 clamping wrench and fastening screws or studs depending on the chuck.

1 set = 3 hard inside jaws, stepped on the outside and 1 set = 3 hard outside jaws, stepped on the inside.

Optional extras:

For spare and additional jaws see No. 314000 – 315200. **For swarf protection** see No. 312800.

Note:

For self-centring three-jaw lathe chucks see No. 313120 – 313140.
DIN 702-3 satisfies the old standard DIN 55027.

Technical description

Aperture E	55 mm
maximum speed	4000 min ⁻¹
Size of studs	M10
Number of studs	4
Height without jaws H ₁	74.5 mm
Chuck key square K	11 mm
Height with jaws H ₂	107 mm
Weight	16.7 kg
Centring Ø B	82.5 mm
Standard	DIN 702-3
Colour code for accessories	Röhm geared scroll chucks and jaws
Type of product	Gear scroll chucks