



## Manual test stand – vertical, Type: 2000



### Order data

Order number	479029 2000
GTIN	2050002071599
Item class	47F

### Description

#### Version:

- **Robust test stand for digital manual force gauge.**
- **Precise linear guide mechanism, can be individually positioned.**

Handwheel version for slow build-up of high test force.

#### Application:

For simple non-speed-dependent tests on materials and components in quality assurance and production.

#### Supplied with:

Supplied with 4 fastening screws for force gauges and instruction manual.

#### Optional extras:

Digital force gauges No. 479025 – 479027 and accessories No. 479033 – 479039.

### Technical description

Feed rate (per revolution)	0.76 mm
Width	203 mm
Height	799 mm

Series	MTH-550
Length	279 mm
maximum application range	2000 N
Weight	10 kg
On/Off switch	no
Feed rate (maximum stroke)	100 mm
Drive	Handwheel
Type of product	Test stand