

**BENNING**
**Digital current clamp, Manufacturer's designation: CM2-1**

**Order data**

Order number	473305 CM2-1
GTIN	4014651446892
Item class	47A

**Description**
**Version:**

Robust and ergonomic plastic casing with illuminated LCD display. Reliable AC and DC measurements without breaking the operating circuit. Recording of measured value and maximum value, relative measurement.

**Application:**

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. AutoV function for automatic AC/DC detection. Low input impedance (LoZ) to suppress "reactive voltages". Low-pass filter (HFR 800 Hz) for measurements on pulsed motor drives. Voltage sensor for non-contact phase and cable-break testing. Memory (HOLD, MAX/MIN). Zero setting.

**Standard:**

**IEC / EN 061010-1 (DIN VDE 0411-1).**

**Supplied with:**

Batteries, probe leads, compact protective case, operating instructions.

**Technical description**

Memory function	HOLD
Memory function	MAX/MIN

Memory function	ZERO
Article no of the battery / rechargeable battery fitted	081561 LR3
Basic accuracy	0.5 %
DC voltage	0.1 mV – 600 V
AC current	10 mA – 400 A
Capacitance	1 nF – 100 mF
maximum jaw aperture	27 mm
Frequency	0.01 Hz – 50 kHz
Overvoltage category	CAT IV 300 V; CAT III 600 V
Number of batteries contained	2
AC voltage	0.1 mV – 600 V
Measurement process	TRUE RMS (AC)
acoustic continuity test	0 – 200 $\Omega$
Power supply	Battery-powered
Information displayed	4000
DC current	10 mA – 400 A
Resistance	0.1 $\Omega$ – 40 M $\Omega$
Calibration	I4
Type of product	Current clamp

## Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

## Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------