



simturn AX copying insert, right-hand, L₂ = 15.2 mm, Ø Dmin: 2,7mm



Order data

| | |
|--------------|---------------|
| Order number | 270591 2,7 |
| GTIN | 2050002066083 |
| Item class | 24U |

Description

Version:

Coating: X800 (successor to coating GN39)

Technical description

| | |
|------------------------------------|---------------------------|
| f | 1.2 mm |
| Radius R | 0.1 mm |
| Ø D | 4 mm |
| max. groove depth t _{max} | 0.5 mm |
| Through-coolant | no |
| Manufacturer's designation | ANTXX800 |
| Usable length | 15.2 mm |
| Product name attribute | L ₂ = 15.2 mm |
| Type of product | Cutter insert for turning |

User data

| | Suitability | V _c | ISO code |
|----------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 400 m/min | N |

| | | | |
|-------------------------------|---|-----------|---|
| Alu > 10% Si | suitable only under restricted conditions | 240 m/min | N |
| Steel < 500 N/mm ² | suitable | 180 m/min | P |
| Steel < 900 N/mm ² | suitable | 130 m/min | P |
| INOX < 900 N/mm ² | suitable | 100 m/min | M |
| INOX > 900 N/mm ² | suitable | 70 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 40 m/min | S |
| GG(G) | suitable | 110 m/min | K |
| CuZn | suitable | 210 m/min | N |
| continuous | suitable | | |
| irregular | suitable only under restricted conditions | | |
| wet maximum | suitable | | |