


**simturn AX copying insert, right-hand, L<sub>2</sub> = 20.3 mm, Ø Dmin: 4,2mm**


## Order data

Order number	270593 4,2
GTIN	2050002066113
Item class	24U

## Description

### Version:

Coating: X800 (successor to coating GN39)

## Technical description

Through-coolant	no
Radius R	0.15 mm
max. groove depth t <sub>max</sub>	0.8 mm
Ø D	4 mm
f	1.95 mm
Manufacturer's designation	AMFJX800
Usable length	20.3 mm
Product name attribute	L <sub>2</sub> = 20.3 mm
Type of product	Cutter insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	400 m/min	N

Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	130 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	100 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	110 m/min	K
CuZn	suitable	210 m/min	N
continuous	suitable		
irregular	suitable only under restricted conditions		
wet maximum	suitable		