

## Garant

### Solid carbide HPC drill, plain shank DIN 6535 HA, TiAlSiN, Ø DC m7: 9mm



## Order data

Order number	122680 9
GTIN	4062406779993
Item class	11E

## Description

### Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

HB and HE shanks are available at the same price as HA.

For **HB**: use order **No. 122681**.

For **HE**: use order **No. 122680** and **129100HE**.

## Technical description

Shank Ø D <sub>s</sub>	10 mm
Standard	DIN 6537
Number of cutting edges Z	2
Nominal Ø D <sub>c</sub>	9 mm
Feed f in titanium > 850 N/mm <sup>2</sup>	0.12 mm/rev.
Tolerance nominal Ø	m7
Flute length L <sub>c</sub>	61 mm
Overall length L	103 mm
recommended maximum drilling depth L <sub>2</sub>	47.5 mm
Coating	TiAlSiN

Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Ti > 850 N/mm <sup>2</sup>	suitable		
Inconel	suitable		
wet maximum	suitable		

### Services

Shank grinding Type HE	129100 HE
------------------------	-----------