



## Manual test stand – vertical, Type: 1500



### Order data

Order number	479029 1500
GTIN	2050002071582
Item class	47F

### Description

#### Version:

- **Robust test stand for digital manual force gauge.**
- **Precise linear guide mechanism, can be individually positioned.**

Lever version with long travel range per lever rotation. Operating handle can be turned to an angle and position, for optimum operation.

#### Application:

For simple non-speed-dependent tests on materials and components in quality assurance and production.

#### Supplied with:

Supplied with 4 fastening screws for force gauges and instruction manual.

#### Optional extras:

Digital force gauges No. 479025 – 479027 and accessories No. 479033 – 479039.

### Technical description

On/Off switch	no
maximum application range	1500 N
Length	279 mm

Width	203 mm
Feed rate (maximum stroke)	150 mm
Feed rate (per revolution)	76 mm
Height	799 mm
Weight	9.1 kg
Series	MTL-330
Drive	Lever
Type of product	Test stand