



Manual test stand – vertical, Type: 500



Order data

Order number	479029 500
GTIN	2050002071575
Item class	47F

Description

Version:

- **Robust test stand for digital manual force gauge.**
- **Precise linear guide mechanism, can be individually positioned.**

Lever version with long travel range per lever rotation. Operating handle can be turned to an angle and position, for optimum operation.

Application:

For simple non-speed-dependent tests on materials and components in quality assurance and production.

Supplied with:

Supplied with 4 fastening screws for force gauges and instruction manual.

Optional extras:

Digital force gauges No. 479025 – 479027 and accessories No. 479033 – 479039.

Technical description

On/Off switch	no
Length	279 mm
Weight	8.2 kg

maximum application range	500 N
Height	578 mm
Feed rate (maximum stroke)	150 mm
Width	203 mm
Series	MTL-110
Feed rate (per revolution)	76 mm
Drive	Lever
Type of product	Test stand