

Garant **UNI LINE****UNI Z-Tower mobile U-shape, Type: L****Order data**

Order number	955455 L
GTIN	4062406785628
Item class	9GC

Description**Version:**

Semi-high UNI Z-Tower with 25 mm thick bamboo worktop. All sides inside and outside with perforated panels □ 9x9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Brush strip at the rear for routing cables and additional cable pass-through. Presentable modular provision system for direct access to work materials and quick visualisation of information. Versatile and general-purpose use for various different applications and fittings. Fitting of drawers only possible in size M. Z-Tower with side panel. Can be used with marking board No. 955444.

With 4 castors, Ø 125 mm, 2 with parking brake.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

Accessories such as marking boards, attachments, pictograms, storage shelves, drawers, doors and push handles can be found under No. 955474 – 955499.

Technical description

Usable depth	510 mm
Series	Z-Tower

Wheel Ø	125 mm
Depth	750 mm
Weight	86 kg
Height	2070 mm
Usable width	690 mm
Width	750 mm
Usable height of tower compartment	850 mm
Worktop thickness	25 mm
Hoffmann perforated panel grid interval	9×9
Height adjustment interval	37
Type of product	Perforated panel tower