

Garant UNILINE

**UNI Z-Tower mobile U-shape, Type: SM****Order data**

Order number	955455 SM
GTIN	4062406785604
Item class	9GC

**Description****Version:**

Semi-high UNI Z-Tower with 25 mm thick bamboo worktop. All sides inside and outside with perforated panels  $\square$  9x9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Brush strip at the rear for routing cables and additional cable pass-through. Presentable modular provision system for direct access to work materials and quick visualisation of information. Versatile and general-purpose use for various different applications and fittings. Fitting of drawers only possible in size M. With 4 castors,  $\varnothing$  125 mm, 2 with parking brake.

**Colour:**

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

**Note:**

Accessories such as marking boards, attachments, pictograms, storage shelves, drawers, doors and push handles can be found under No. 955474 – 955499.

**Technical description**

Usable depth	510 mm
Weight	69 kg

Height	1095 mm
Depth	750 mm
Series	Z-Tower
Wheel Ø	125 mm
Usable width	540 mm
Width	750 mm
Usable height of tower compartment	850 mm
Worktop thickness	25 mm
Hoffmann perforated panel grid interval	9×9
Height adjustment interval	37
Type of product	Perforated panel tower