

Garant
Solid carbide extension for screw-in milling cutters $\varnothing d = 25$ mm, Thread M \times L: M12X156

Order data

| | |
|--------------|----------------|
| Order number | 301366 M12X156 |
| GTIN | 4062406786014 |
| Item class | 31Z |

Description
Version:

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

| | |
|--------------------------|-------------------------|
| External $\varnothing D$ | 23 mm |
| Overall length L_{tot} | 156 mm |
| Reach L_1 | 100 mm |
| Thread M | M12 |
| Bore $\varnothing D_1$ | 12.5 mm |
| Shank $\varnothing d$ | 25 mm |
| Adapter | $\varnothing d = 25$ mm |
| Through-coolant | yes |
| Vibration | damped |
| Type of product | Extension |

