

**Garant**

**Solid carbide extension for screw-in milling cutters  $\varnothing d = 20$  mm, Thread M  $\times$  L: M10X160**


**Order data**

Order number	301364 M10X160
GTIN	4062406785703
Item class	31Z

**Description**
**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

**Technical description**

External $\varnothing D$	17.8 mm
Bore $\varnothing D_1$	10.5 mm
Reach $L_1$	100 mm
Shank $\varnothing d$	20 mm
Overall length $L_{tot}$	160 mm
Thread M	M10
Adapter	$\varnothing d = 20$ mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

