

**Garant****Solid carbide extension for screw-in milling cutters  $\varnothing d = 12$  mm, Thread M  $\times$  L: M6X70****Order data**

Order number	301381 M6X70
GTIN	4062406786052
Item class	31Z

**Description****Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

**Technical description**

External $\varnothing D$	9.8 mm
Shank $\varnothing d$	12 mm
Bore $\varnothing D_1$	6.5 mm
Thread M	M6
Overall length $L_{tot}$	70 mm
Reach $L_1$	20 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

