

**Garant****Solid carbide extension for screw-in milling cutters  $\varnothing d = 16$  mm, Thread M  $\times$  L: M8X135****Order data**

Order number	301383 M8X135
GTIN	4062406786106
Item class	31Z

**Description****Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

**Technical description**

Bore $\varnothing D_1$	8.5 mm
External $\varnothing D$	12.8 mm
Shank $\varnothing d$	16 mm
Overall length $L_{tot}$	135 mm
Thread M	M8
Reach $L_1$	80 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

