

Garant

Solid carbide extension for screw-in milling cutters $\varnothing d = 20$ mm, Thread M \times L: M10X135

**Order data**

Order number	301384 M10X135
GTIN	4062406786144
Item class	31Z

Description**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

Overall length L_{tot}	135 mm
Shank $\varnothing d$	20 mm
Bore $\varnothing D_1$	10.5 mm
Thread M	M10
Reach L_1	80 mm
External $\varnothing D$	15.4 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

