

Garant

Shrink-fit chuck vibration-damped, with cooling channel bores, HSK-A 100 A = 120, Clamping range Ø D1: 6mm

**Order data**

Order number	308346 6
GTIN	4062406787264
Item class	31A

Description**Version:**

- **High-temperature steel.**
- **Integrated length adjustment of the tools.**
- **For HSS and solid carbide tools.**
- **Shanks hard turned (smooth cutting action!).**
- **With RFID/Balluffchip bore.**
- **With coolant channel bores and threads that can be sealed.**
- **With tapped holes on each side for balancing screws.**
- **Reinforced version/contour.**
- **Polished surface.**
- **Specially mounted carbide core in the shrink-fit chuck body.**

Advantage:

- **Vibration-damping.**
- **Better workpiece surface finish.**
- **Optimised tool life.**
- **Increased process reliability.**
- **Lower corrosion tendency due to polished surface.**

Application:

For clamping tools with plain shank (h6 shank tolerance). Suitable for inductive, contact and hot air shrink-fitting units.

Optional extras:

HSK coolant tube No. 309880,
Socket wrench No. 309890,

Shrink-fit unit, accessories No. 354210 – 354440,
Balancing screws set No. 309906 size 180.

Technical description

Cooling channel bore	lockable
Overhang dimension A	120 mm
Ø D ₂	21 mm
Clamping Ø D ₁	6 mm
L ₂	50 mm
Ø D ₃	88 mm
External Ø D	27 mm
Adapter	HSK-A 100 A = 120
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Through-coolant	yes
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Machining strategy	HPC
Vibration	damped
Type of product	Shrink-fit chuck