

**Dry vacuum cleaner, Manufacturer's designation: VHS120CB****Order data**

Order number	078558 VHS120CB
GTIN	5711145403940
Item class	07D

Description**Version:**

High quality, very durable Nilfisk CFM "grey line" industrial vacuum cleaner.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Note:

See under 078551-078552 for suitable accessories.

Technical description

Container volume	37 l
AC supply voltage	230 V
On/Off switch	yes
Connection width	50 mm
Width	570 mm
Filter system	Star-shaped filter

Power supply	Mains-powered
Length	560 mm
Dust class – vacuum cleaner	M
Filter cleaning	manual filter shaker
Weight	38 kg
Operating noise	74 dB(A)
Power consumption	2000 W
IP Index of Protection	IP 44
Height	1015 mm
Type of filter	polyester filter
Mains frequency	50 Hz
Type of product	Wet and dry vacuum cleaners