

Garant GRIDLINE

ToolTruck mobile workbench with full extension drawers for L-BOXX®, 16×16G, Type: 10



Order data

| | |
|--------------|---------------|
| Order number | 914575 10 |
| GTIN | 4062406785598 |
| Item class | 9GT |

Description

Version:

The ToolTruck mobile workbench has a worktop of X-ABS for highly demanding technical applications. Open compartment with 4 pull-out shelves, suitable for 4 pcs. L-BOXX® modular plastic cases, which can be quickly and easily engaged and released. 2 pcs. each L-BOXX® modular plastic case No. 693330 size 102 and size 136 will fit. Or alternatively: 2 pcs. No. 693330 size 102; 1 pc. size 238 (if 3rd pull-out shelf removed). **Cabinet stiles are clad with LDPE bumpers. Central locking** locks door, drawers and pull-out shelves.

With 6 drawers.

Supplied with:

With dividers:

each 75 mm drawer 1 slotted partition No. 951510 size 75;

each 125 mm drawer 1 slotted partition No. 951510 size 125.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

Optional storage shelf / side compartment No. 914791 not integrated into the ToolTruck central locking system, locked instead by a separate cylinder lock. See group 95 for further accessories and dividing material. Carrying case L-BOXX® is not included.

Technical description

| | |
|--|----------------|
| Width | 1195 mm |
| Depth | 500 mm |
| Drawer front height | 75 mm |
| Drawer front height | 75 mm |
| Drawer front height | 75 mm |
| Drawer front height | 125 mm |
| Drawer front height | 200 mm |
| Drawer front height | 200 mm |
| Height | 1000 mm |
| Material of worktop | X-ABS |
| Bumper | yes |
| Drawer usable width | 400 mm |
| Number of castors with parking brake | 2 |
| Drawer usable width in G | 16 |
| Number of drawers | 6 |
| Drawer usable area in G | 16×16 |
| Weight | 104 kg |
| Drawer usable depth in G | 16 |
| Individual drawer release system | One-hand |
| Drawer usable depth | 400 mm |
| Series | ToolTruck |
| ComfortClose | no |
| Number of fixed wheels without parking brake | 2 |
| can be lowered | no |
| Number of doors | 0 |
| Pull-out shelf usable width | 370 mm |
| Drawer/pull-out shelf load capacity | 40 kg |
| Drawer runner extension (partial/full extension) | 100 % |
| Drawer runner extension | Anti-tilt lock |

| | |
|---|------------------|
| Hoffmann perforated panel grid interval | 9×9 mm |
| Cylinder lock | modular barrel |
| Product name attribute | 16×16G |
| Type of product | mobile workbench |

Accessories

| | |
|---|-------------|
| Slotted dividersDepth 16G suitable for drawer front height 75 mm | 951510 75 |
| Slotted dividersDepth 16G suitable for drawer front height 125 mm | 951510 125 |
| Set of wheels for roller cabinets and mobile workbenches Type G | 915567 G |
| Lock plate for GridLine Type VA21 | 914227 VA21 |