




ECO cut knurling tool right-hand, Shank size: 20mm



Order data

Order number	290231 20
GTIN	4030741902116
Item class	29H

Description

Version:

Grub screws in the shank for clearance angle correction.

Technical description

Carbide sleeve, cover disc, screw	299920 7
Working range	10 - 300 mm
for knurl width w	6 mm
for knurl $\varnothing d_1$	25 mm
for knurl bore $\varnothing d_2$	8 mm
for knurl profile	RAA 1×BR30°
for knurl profile	RAA 1×BL30°
for knurl profile	RBR30° 1×AA
for knurl profile	RBL30° 1×AA
for knurl profile	RBR45° 1×BL15°
for knurl profile	RBL45° 1×BR15°
Type of product	Self-centering knurling tool

