

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 3,8mm**

**Order data**

Order number	122481 3,8
GTIN	4062406790707
Item class	11E

**Description**
**Version:**

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Overall length L	66 mm
Nominal Ø $D_c$	3.8 mm
Number of cutting edges Z	2
Tolerance nominal Ø	m7
Feed f in titanium > 850 N/mm <sup>2</sup>	0.05 mm/rev.
recommended maximum drilling depth $L_2$	18.3 mm
Standard	DIN 6537 K
Flute length $L_c$	24 mm
Shank Ø $D_s$	6 mm
Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Ti > 850 N/mm <sup>2</sup>	suitable		
Inconel	suitable		
wet maximum	suitable		