



ECO knurl forming tool universal, Shank size: 12Xmm



Order data

Order number	290036 12X
GTIN	4030741933240
Item class	29H

Description

Version:

Used conventionally.

Note:

Tip height must be adjusted.

Technical description

Working range	8 - 200 mm
for knurl bore $\varnothing d_2$	6 mm
for knurl $\varnothing d_1$	20; 25 mm
Roller pin	299911 8
for knurl width w	8 mm
Shank width	12 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR 1×BL
for knurl profile	RBL 1×BR
for knurl profile	RBL 1×BR
for knurl profile	RGE30° 1×GV30°
for knurl profile	RBR 1×BL
Type of product	Self-centering knurling tool

