

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 10,8mm**

**Order data**

Order number	122481 10,8
GTIN	4062406791353
Item class	11E

**Description**
**Version:**

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Number of cutting edges Z	2
Tolerance nominal Ø	m7
Standard	DIN 6537 K
Feed f in titanium > 850 N/mm <sup>2</sup>	0.14 mm/rev.
recommended maximum drilling depth L <sub>2</sub>	38.8 mm
Nominal Ø D <sub>c</sub>	10.8 mm
Overall length L	102 mm
Shank Ø D <sub>s</sub>	12 mm
Flute length L <sub>c</sub>	55 mm
Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

### User data

	Suitability	V <sub>c</sub>	ISO code
Ti > 850 N/mm <sup>2</sup>	suitable		
Inconel	suitable		
wet maximum	suitable		