

Garant**Solid carbide extension for screw-in milling cutters $\varnothing d = 16$ mm, Thread M \times L: M8X75****Order data**

Order number	301383 M8X75
GTIN	4062406786076
Item class	31Z

Description**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

Thread M	M8
Reach L_1	20 mm
Bore $\varnothing D_1$	8.5 mm
Shank $\varnothing d$	16 mm
External $\varnothing D$	12.8 mm
Overall length L_{tot}	75 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

