

**Garant**
**Solid carbide extension for screw-in milling cutters  $\varnothing d = 16$  mm, Thread M  $\times$  L: M8X95**

**Order data**

Order number	301383 M8X95
GTIN	4062406786083
Item class	31Z

**Description**
**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

**Technical description**

Shank $\varnothing d$	16 mm
External $\varnothing D$	12.8 mm
Bore $\varnothing D_1$	8.5 mm
Reach $L_1$	40 mm
Overall length $L_{tot}$	95 mm
Thread M	M8
Through-coolant	yes
Vibration	damped
Type of product	Extension

