

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 6,5mm

Order data

Order number	122481 6,5
GTIN	4062406790974
Item class	11E

Description
Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Overall length L	79 mm
Number of cutting edges Z	2
Feed f in titanium > 850 N/mm ²	0.09 mm/rev.
Shank Ø D _s	8 mm
Tolerance nominal Ø	m7
recommended maximum drilling depth L ₂	24.5 mm
Nominal Ø D _c	6.5 mm
Flute length L _c	34.25 mm
Standard	DIN 6537 K
Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable		
Inconel	suitable		
wet maximum	suitable		