

Garant

Solid carbide extension for screw-in milling cutters $\varnothing d = 25$ mm, Thread M \times L: M12X165

**Order data**

Order number	301386 M12X165
GTIN	4062406786175
Item class	31Z

Description**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

Reach L_1	100 mm
Thread M	M12
Overall length L_{tot}	165 mm
Shank $\varnothing d$	25 mm
External $\varnothing D$	20.8 mm
Bore $\varnothing D_1$	12.5 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

