

Garant**Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1: M10X75****Order data**

Order number	301309 M10X75
GTIN	4062406786182
Item class	31A

Description**Version:**

Plain design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

Bore $\varnothing D_1$ tolerance IT6	10.5 mm
$\varnothing D_2$	18 mm
L_2	5 mm
Thread M	M10×75
External $\varnothing D$	28 mm
Reach L_1	75 mm
Overhang dimension A	94 mm
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor