

Garant

Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 3,3mm



Order data

Order number	122681 3,3
GTIN	4062406791520
Item class	11E

Description

Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

recommended maximum drilling depth L_2	23.1 mm
Tolerance nominal \varnothing	m7
Overall length L	66 mm
Flute length L_c	28.05 mm
Standard	DIN 6537
Feed f in titanium $> 850 \text{ N/mm}^2$	0.04 mm/rev.
Number of cutting edges Z	2
Shank $\varnothing D_s$	6 mm
Nominal $\varnothing D_c$	3.3 mm
Coating	TiAlSiN
Tool material	Solid carbide
Version	6xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable		
Inconel	suitable		
wet maximum	suitable		