

Garant

Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 8,6mm



Order data

Order number	122681 8,6
GTIN	4062406792053
Item class	11E

Description

Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Overall length L	103 mm
Nominal Ø D_c	8.6 mm
Flute length L_c	61 mm
Tolerance nominal Ø	m7
Number of cutting edges Z	2
Standard	DIN 6537
Feed f in titanium > 850 N/mm ²	0.11 mm/rev.
recommended maximum drilling depth L_2	48.1 mm
Shank Ø D_s	10 mm
Coating	TiAlSiN
Tool material	Solid carbide
Version	6xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable		
Inconel	suitable		
wet maximum	suitable		