

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 12,5mm

Order data

Order number	122481 12,5
GTIN	4062406791421
Item class	11E

Description
Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Tolerance nominal Ø	m7
Number of cutting edges Z	2
Standard	DIN 6537 K
Overall length L	107 mm
Shank Ø D _s	14 mm
Nominal Ø D _c	12.5 mm
Flute length L _c	60.05 mm
recommended maximum drilling depth L ₂	41.3 mm
Feed f in titanium > 850 N/mm ²	0.15 mm/rev.
Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable		
Inconel	suitable		
wet maximum	suitable		