

Garant

Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlSiN, Ø DC m7: 4,8mm



Order data

Order number	122481 4,8
GTIN	4062406790806
Item class	11E

Description

Version:

Specially for machining **titanium-based and nickel-based alloys**. With wear-resistant, ultra-smooth TiAlSiN high-performance coating for a **long tool life** combined with **optimum bore quality** and **very low burr formation**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Shank Ø D_s	6 mm
Nominal Ø D_c	4.8 mm
Feed f in titanium $> 850 \text{ N/mm}^2$	0.06 mm/rev.
Standard	DIN 6537 K
recommended maximum drilling depth L_2	20.8 mm
Number of cutting edges Z	2
Flute length L_c	28 mm
Tolerance nominal Ø	m7
Overall length L	66 mm
Coating	TiAlSiN
Tool material	Solid carbide
Version	4xD

Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	pink
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Ti > 850 N/mm ²	suitable		
Inconel	suitable		
wet maximum	suitable		