


HAIMER MILL solid carbide torus cutter, AlTiN, Ø f9 DC / R1: 12/0,5mm

Order data

Order number	220296 12/0,5
GTIN	4034221143167
Item class	26X

Description
Version:

For **general-purpose use** in steel materials and high-alloy steels, especially stainless steel. With **cylindrical core** for optimum tool stiffness when milling slots. Reliable processes guaranteed when ramping and during circular interpolation milling thanks to **special end face geometry**.

Note:

For **HB** use order **No. 220297**.

Tool arbor with the SAFE-LOCK pull-out protection can be found under clamping technology.

Technical description

Recess Ø D ₁	11.4 mm
Feed f _z for side milling in steel < 900 N/mm ²	0.078 mm
Corner radius R ₁	0.5 mm
No. of teeth Z	4
Flute length L _c	26 mm
Shank Ø D _s	12 mm
Overall length L	84 mm
Feed f _z for slot milling in steel < 900 N/mm ²	0.066 mm
Helix angle	32 degrees
Shank	DIN 6535 HA to h6
Cutting edge Ø D _c	12 mm

Overhang length L_1 incl. recess	36.5 mm
Coating	AlTiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Tolerance nominal \varnothing	f9
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions	480 m/min	N
Alu > 10% Si	suitable only under restricted conditions	375 m/min	N
Steel < 500 N/mm ²	Suitable		
Steel < 750 N/mm ²	Suitable		
Steel < 900 N/mm ²	Suitable		
Steel < 1100 N/mm ²	Suitable		
INOX < 900 N/mm ²	Suitable		
INOX > 900 N/mm ²	Suitable		

Ti > 850 N/mm ²	suitable only under restricted conditions
GG(G)	suitable only under restricted conditions
Uni	Suitable
Oil	Suitable
wet maximum	suitable
wet minimum	Suitable
dry	Suitable
Air	Suitable