



## HAIMER MILL solid carbide torus cutter SAFE-LOCK, AlTiN, Ø f9 DC / R1: 4/0,4mm



### Order data

Order number	220298 4/0,4
GTIN	4034221161796
Item class	26X

### Description

#### Version:

With SAFE-LOCK pull-out protection to provide an additional form fit for the tool. In conjunction with SAFE-LOCK tool holders, it secures the tool to prevent it being pulled out.

For **general-purpose use** in steel materials and high-alloy steels, especially stainless steel. With **cylindrical core** for optimum tool stiffness when milling slots. Reliable processes guaranteed when ramping and during circular interpolation milling thanks to **special end face geometry**.

#### Note:

Tool arbor with the SAFE-LOCK pull-out protection can be found under clamping technology.

### Technical description

Overhang length $L_1$ incl. recess	15 mm
Overall length $L$	58 mm
No. of teeth $Z$	4
Corner radius $R_1$	0.4 mm
Recess $\varnothing D_1$	3.8 mm
Shank $\varnothing D_s$	6 mm
Flute length $L_c$	11 mm
Helix angle	32 degrees
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.026 mm

Feed $f_z$ for slot milling in steel $< 900 \text{ N/mm}^2$	0.022 mm
Cutting edge $\varnothing D_c$	4 mm
Shank	Safe-Lock h6
Coating	AlTiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Tolerance nominal $\varnothing$	f8
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	$0.5 \times D$ for side milling
Through-coolant	no
Machining strategy	HPC
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions	480 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	480 m/min	N
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions	375 m/min	N
Steel $< 500 \text{ N/mm}^2$	Suitable	275 m/min	P
Steel $< 750 \text{ N/mm}^2$	Suitable	255 m/min	P
Steel $< 900 \text{ N/mm}^2$	Suitable	210 m/min	P
Steel $< 1100 \text{ N/mm}^2$	Suitable	190 m/min	P
INOX $< 900 \text{ N/mm}^2$	Suitable	95 m/min	M

INOX > 900 N/mm <sup>2</sup>	Suitable	75 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable only under restricted conditions	155 m/min	K
Uni	Suitable		
Oil	Suitable		
wet maximum	Suitable		
wet minimum	Suitable		
dry	Suitable		
Air	Suitable		