

Garant**Cleaning propeller, Blade Ø: 160mm****Order data**

| | |
|--------------|---------------|
| Order number | 358950 160 |
| GTIN | 4062406792435 |
| Item class | 31E |

Description**Version:**

- **Robust design.**
- **Opening and closing the vane by the speed of the spindle.**
- **Marked ends to the vanes, for optimum visibility.**
- **For installation in any toolholder with through-coolant capability.**

The machine must be started at 2000 rpm and slowly increased to 6000 rpm – 12000 rpm.

Advantage:

- **Efficient cleaning of clamping equipment, workpieces and work tables.**
- **Removal of accumulated chips and blowing out pockets of water.**
- **Perfect complement to the automated work process.**

Optional extras:

Spare cleaning propeller No. 358951 1K and 4K.

Technical description

| | |
|-------------|--------------------------------|
| Speed range | 6000 - 12000 min ⁻¹ |
| Shank Ø | 20 mm |

| | |
|-----------------|--------------------|
| Type of product | Cleaning propeller |
|-----------------|--------------------|

Accessories

| | |
|--------------------------|----------|
| Spare spring set 4 pcs 4 | 358953 4 |
|--------------------------|----------|