



DUO-LOCK HAIMER MILL Power Series TPC, AlTiN, Ø h9 D1: 16mm



Order data

Order number	220327 16
GTIN	4034221103222
Item class	26Y

Description

Version:

DUO-LOCK HAIMER MILL: Can be used as a universal tool. Unique end face geometry for ramping and circular interpolation milling. First choice for applications with short overhangs.

DUO-LOCK HAIMER MILL Power Series: First choice for applications with long overhangs and unstable clamping conditions. For particularly smooth running on long overhangs it is preferable to use solid carbide extensions.

Note:

h_{max} : The values stated in the table are maximum values.

$ae_{max} = 0.05 \times D$ for TPC machining.

Technical description

Average chip thickness h_{max} for TPC milling in steel < 900 N/mm ²	0.035 mm
Corner chamfer angle	45 degrees
Overall length L	56 mm
Ø D ₂	15.5 mm
Number of cutting edges Z	5
Overhang L ₁	48 mm
recommended tightening torque	60 Nm
Flute length L ₂	48 mm

DUO-LOCK interface	DL16
Tolerance nominal \varnothing	h9
Corner chamfer width at 45°	0.5 mm
Cutter \varnothing D	16 mm
Width across flats AF	13 mm
Coating	AlTiN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle	46 degrees
Helix angle characteristic	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05xD
Machining strategy	TPC
Through-coolant	no
suitable arbor	with threaded shank
Type of product	Cutter insert for milling

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	700 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	700 m/min	N
Alu > 10% Si	suitable only under restricted conditions	235 m/min	N
Steel < 500 N/mm ²	suitable	220 m/min	P
Steel < 750 N/mm ²	suitable	180 m/min	P
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	120 m/min	P

INOX < 900 N/mm ²	suitable only under restricted conditions	80 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions	130 m/min	K
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable		
Air	suitable		