


**HAIMER MILL end mill, AlTiN, Ø f9 DC: 2mm**

**Order data**

Order number	220286 2
GTIN	4034221123244
Item class	26X

**Description**
**Version:**

For **general-purpose use** in steel materials and high-alloy steels, especially stainless steel. With **cylindrical core** for optimised tool stiffness when milling slots. Reliable processes guaranteed when ramping and during circular interpolation milling thanks to **special end face geometry**.

**Note:**

Tool holders with the SAFE-LOCK pull-out protection can be found under clamping technology. For **HB** use order **No. 220287**.

**Technical description**

Helix angle	32 degrees
Direction of infeed	horizontal, oblique and vertical
Flute length $L_c$	7 mm
Overhang length $L_1$ incl. recess	9 mm
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.013 mm
Shank	DIN 6535 HA to h6
Corner chamfer width at $45^\circ$	0.04 mm
No. of teeth $Z$	4
Feed $f_z$ for slot milling in steel $< 900 \text{ N/mm}^2$	0.011 mm
Recess $\varnothing D_1$	1.9 mm
Shank $\varnothing D_s$	6 mm

Tolerance nominal $\varnothing$	f8
Corner chamfer angle	45 degrees
Overall length L	58 mm
Cutting edge $\varnothing D_c$	2 mm
Coating	AlTiN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.5×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	without
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions	480 m/min	N
Alu > 10% Si	suitable only under restricted conditions	350 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	275 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	255 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	190 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	95 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	75 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable		
Air	suitable		